



## CW/WP SERIES POLYPROPYLENE WOUND CARTRIDGES

- String-wound design reduces fine sediment from a variety of fluids
- Withstands temperatures up to 165° F (73.9° C)
- Economically priced
- Nominal 10, 30, 50-micron rating (CW) and nominal 5, 30-micron rating (WP)

CW and WP Series cartridges are manufactured from a durable polypropylene cord that is wound around a rigid polypropylene core. They are an economical solution to reduce fine sediment, including sand, silt, rust and scale particles.

CW cartridges are very economical and wound in a standard pattern around the core. They are available in 10, 30 and 50-micron ratings.

WP Series cartridges are wound in a precise pattern around the core providing greater surface area. The result is higher dirt-loading capacity and greater efficiency than standard wound cartridges like the CW.

Both of these string-wound cartridge styles are capable of withstanding temperatures up to 165° F (73.9° C), and will accommodate flow rates between 7 and 10 GPM with minimal pressure drop.


CW and WP Series cartridges are suitable for a wide variety of sediment filtration applications, including municipal and well water as well as many industrial fluids.



Pure Quality.™

# CW/WP SERIES

## Polypropylene Wound Cartridges



### Cartridge Specifications and Performance Data

Model	Maximum Dimensions	Micron Rating (Nominal)	Initial ΔP (psi) @ Flow Rate (gpm)
CW-F	2-1/4" x 9-7/8" (60 mm x 251 mm)	10	<1 psi @ 10 gpm (<0.07 bar @ 27 L/min)
CW-MF	2-1/4" x 9-7/8" (60 mm x 251 mm)	30	<1 psi @ 10 gpm (<0.07 bar @ 38 L/min)
CW-50	2-1/4" x 9-7/8" (60 mm x 251 mm)	50	<1 psi @ 10 gpm (<0.07 bar @ 38 L/min)
WP-5	2-1/4" x 9-7/8" (60 mm x 251 mm)	5	<2.5 psi @ 10 gpm (<0.17 bar @ 38 L/min)
WP-30	2-1/4" x 9-7/8" (60 mm x 251 mm)	30	<1.4 psi @ 10 gpm (<0.10 bar @ 38 L/min)

### Materials of Construction

- Filter Media: Polypropylene Fiber Cord
- Core: Polypropylene
- Temperature Rating: 40°F to 165°F (4.4°C to 73.9°C)

**WARNING:** Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.



502 Indiana Avenue • P.O. Box 1047 • Sheboygan, Wisconsin 53082-1047  
 Customer Service: 800-645-0267 • Fax: 888-203-7361 • supportspecialist@pentekfiltration.com  
 International: 920-457-9435 • Fax: 920-457-2417 • international@pentekfiltration.com

